

MONTAGEANLEITUNG

-  MONTAGEANLEITUNG
-  ASSEMBLY INSTRUCTION
-  DE INSTRUCTIE VAN DE ASSEMBLAGE
-  ISTRUZIONE DELL'ASSEMBLEA
-  INSTRUCCIÓN DE ASAMBLEA
-  INSTRUCTION DE MONTAGE
-  NÁVOD K MONTÁŽI
-  MONTERINGSANVISNING

-  MONTAJ TALIMATI
-  ASENNUŠOJE
-  BRUGSANVISNING
-  BRUKSANVISNING
-  UPUTE ZA MONTAŽU
-  NAVODILA ZA MONTAŽO
-  SZERELÉSI ÚTMUTATÓ
-  INSTRUCTIUNI DE MONTAJ



Version 16.6

Modell-Nr.

70590

ART.-NR. FRONT KORPUS

70592

Rot
(ähnl. RAL 3002)

Silber

70597

Ultramarinblau
(RAL 5002)

Silber

70596

Silber

Schwarz
(RAL 9005)

Friedrich Küpper GmbH
Friedrich-Küpper-Weg
54570 Berlingen
Deutschland

Telefon +49 (0) 65 91 - 95 42 0
Telefax +49 (0) 65 91 - 95 42 17
E-Mail info@friedrich-kuepper-gmbh.de
Internet www.friedrich-kuepper-gmbh.de

EINZELTEILE / PIECES


1× **B**



910 mm × 450 mm

Art.-Nr. E0035 (Silver/silver)
Art.-Nr. E0036 (Schwarz/black)

1× **I**



1770 mm × 70 mm

Art.-Nr. E0059 (Silver/silver)
Art.-Nr. E0060 (Schwarz/black)

1× **C**



830 mm × 405 mm

Art.-Nr. E0040 (verzinkt/galvanised)

1× **K**



910 mm × 100 mm

Art.-Nr. E0071 (Silver/silver)
Art.-Nr. E0072 (Schwarz/black)

2× **E**



1770 mm × 430 mm

Art.-Nr. E0043 (Silver/silver)
Art.-Nr. E0108 (Schwarz/black)


1× **L**



1665 mm × 450 mm

Art.-Nr. E0078 (Silver/silver)
Art.-Nr. E0075 (Rot/red)
Art.-Nr. E0077 (Blau/blue)

2× **G**



1770 mm × 385 mm

Art.-Nr. E0052 (Silver/silver)
Art.-Nr. E0053 (Schwarz/black)

1× **M**



1665 mm × 458 mm

Art.-Nr. E0096 (Silver/silver)
Art.-Nr. E0093 (Rot/red)
Art.-Nr. E0095 (Blau/blue)

1× **F1**



870 mm × 380 mm

Art.-Nr. E0051 (verzinkt/galvanised)

3× **N**



900 mm × 380 mm

Art.-Nr. E0101 (verzinkt/galvanised)

10× **O**



830 mm × 395 mm

Art.-Nr. E0104 (verzinkt/galvanised)



1× **E1**





870 mm × 380 mm


Art.-Nr. E0046 (verzinkt/galvanised)

BEUTELINHALT / BAG CONTENT

 4× M6 × 16 mm Art.-Nr. E0750	 16× M6 × 12 mm Art.-Nr. E0751	 4× M6 × 16 mm Art.-Nr. E0752	 24× ø 6,4 mm Art.-Nr. E0753	 24× M6 Art.-Nr. E0754	 10× 6,9 × 13 mm Art.-Nr. E0774
 4× M4 × 10 mm Art.-Nr. E0755	 4× ø 4,3 mm Art.-Nr. E0757	 4× M4 Art.-Nr. E0290	 4× 5 × 15 Art.-Nr. E0760	 4× 5 × 5 Art.-Nr. E0759	 4× Art.-Nr. E0758
 4× Art.-Nr. E0761	 4× Art.-Nr. E0762	 4× Art.-Nr. E0763	 2× Art.-Nr. E0765	 1× Art.-Nr. E0766	 1× Art.-Nr. E0767
 1× Art.-Nr. E0770	 1× Art.-Nr. E0771	 1× Art.-Nr. E0772	 1× Art.-Nr. E0773		

BENÖTIGTES WERKZEUG / NEEDED TOOLS

1  PH 1 × 100 PH 2 × 100 Schlitz 6,5 × 150	2  SW 7 SW 10	3  6 mm
4 	5 	6  5 mm
7 	8 	9 



2.



3.

4× M6

4× M6 × 12

4× 6,4 MM

② 2× SW 10



4.



5.



6.



7.



8.

4x M6 x 12




9.

4x M6

4x 6,4 MM

②  SW10



10.



11.

4x M6 4x M6x16 4x 6,4 mm 2x

⑥



12.


4x



13.

2x

① PH 2x100




14.

2x



15.

4x M6 4x M6x16 4x 6,4 mm 2x ① PH 2x100 ② SW10



16.



17.

4x M6 x 12 4x 6,4 MM



18.

4x M6 x 12 4x 6,4 MM



19.

8x M6

② SW10



20.

2x 5x15

⑤



21. 
2x 5x5




22. 
2x 5x15

5 



23. 
2x 5x5




24.  1x



25.  1x M4  1x M4x10  1x 4,3 mm  ① PH 1x100  ② SW 7




26.



27.  1x  1x M4  1x M4x10  1x 4,3 mm

①  PH 1x100 ②  SW 7



28.  1x



29.  1x M4  1x M4x10  1x 4,3mm  ① PH1x100  ② SW 7




30.



31.  1x  1x M4  1x M4x10  1x 4,3mm

①  PH1x100 ②  SW 7



32.



9



33.

1x _____




34.

1x _____



35.  1x  1x  1x

⑨ 



36.

① 
Schlitz 6,5 x 150



37.



38.



39.

 10x 6,9 x 13

②  SW10



40.

③ 10x DL



41.

③ 10x DR




42.



43.



A.



B.



C.



D.



Modell-Nr.

70590